# **REFCON RMM Modem**

Local powerline monitoring solution for refrigerated containers

- ■The same product can be used for all brands and types of reefer containers
- Easy installation as all brands of reefer containers are prepared for remote monitoring modem
- Compatibility with all brands and types of power-line based remote monitoring systems
- Compliant with ISO10368 High Data Rate standard
- Easy diagnostic due to six LED 's providing information regarding operating status and malfunctions

#### Description

The Remote Monitoring Modem is a ISO10368 standard remote communication device, better known as the RMM.

The RMM is the key component in power-line communication for monitoring and control of reefer containers.

Each container equipped with an RMM is able to send data on its operating conditions and alarms to a central monitoring system, such as the market-leading REFCON system.

Besides monitoring, the RMM can be used to remotely control various reefer container functions, which include changing the setpoint, initiating defrost, and activating automatic pre-trip inspection.

In combination with a reefer monitoring system such as REFCON, the RMM offers a number of important benefits, such as:

- Reduced risk of potential cargo damage thanks to continuous automatic monitoring of your reefer containers
- Reduction of operational cost due to less time-consuming manual inspections
- Improved safety of personnel
- Improve cargo documentation handling processes
- Optimization of reefer container operation with reduced risk of human errors



### **Applications**

- Enables reefer containers to be power-line remote monitored on vessels, in terminals, and on trucks and trains
- Remote monitoring of reefer container operating conditions and alarms




#### **Data Sheet:**

## **Environmental Specifications:**

Operation temperature	-40°C <t<sub>op &lt; 85°C</t<sub>
Shock	20G operating, 100G non-operating
Physical dimensions:	
Length	320 mm
Width	115 mm
Height	43 mm
Weight	600 gr
Supported controllers:	
Carrier	Microlink 3 Microlink 2I
Daikin	DECOS IIIe DECOS IIId DECOS IIIc DECON IIIb DECOS 3 b, c, d, e, f, g, h, i, j
Starcool	RCCU5 SCC6
Thermo King	Magnum Plus and Super Freezer supported with specialized solutions

#### **Dimensions:**



Emerson Climate Technologies  $\cdot$  Transportation Solutions  $\cdot$  Denmark  $\cdot$  Phone +45 70 23 44 44  $\cdot$  ts.support@emerson.com

Climate.Emerson.com

 $2016 ECT-4 \quad Emerson \ is \ a \ trademark \ of \ Emerson \ Electric \ Co. \ @2015 \ Emerson \ Climate \ Technologies, \ Inc. \ All \ rights \ reserved.$